

H.B. Fuller | Royal Adhesives & Sealants Canada Ltd
266 Humberline Drive, Toronto, ON, M9W 5X1
P: +1 416-649-5676 | F: +1 416-679-0511
hbfuller.com

Q-GEAR 2100™

Manual X-Motion Dispensing Machine

PRODUCT DESCRIPTION

Q-Gear 2100™ is an advanced and affordable manual X-motion dispensing machine, specifically designed to work with Chem-Dec™ and E-Dome™ 2-component, polyurethane doming resins. Q-Gear™ 2100 is ideal for doming multiple parts simultaneously.

FEATURES & BENEFITS

- Simple to operate, excellent for new start-ups
- DC driven axis & pump allows for rapid response and accurate resin flow control
- Short cycle time, higher productivity
- Smart static mixers (low cost replacement parts)



WARRANTY

The Q-Gear™ 3400 comes with our standard warranty, as outlined in Royal Adhesives & Sealants Canada Ltd.'s Equipment Warranty Statement.

TECHNICAL DATA

Nozzle Movement	Manual X-Motion
Motion Programming	Manual
Dosing	Gear Pumps
Isocyanate : Polyol Ratio	E-Dome™ & Chem-Dec™
	2 component resins
	1:1
Pot Life Alarms	Standard
Rinse & Purge Systems	Manual
Working table dimensions (approximate)	16" x 24" 400 mm x 600 mm (optional vacuum table, air blower)
Size & Weight (approximate)	44" x 45" x H67" 1130 mm x 1150 mm x H1700 mm 800 lbs / 363 kg

Q-GEAR 2100™

Manual X-Motion Dispensing Machine

ACCESSORIES & SPARE PARTS INCLUDED WITH THE DISPENSER

- 1 Dispensing nozzle holder with a 4-nozzle manifold,
4 holders and 4 dispensing nozzles
- 1 Static mixer insert kit (Q-0006-1)
- 1 Dispense valve seal kit (ZVA-00001-01-12)
- 1 Valve spanner wrench (ZTL-00008)

The conditions of your use and application of our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested method of application and recommendations, are beyond our control. Therefore, it is imperative that you test our products, technical assistance and information to determine to your own satisfaction whether they are suitable for your intended uses and applications. This application-specific analysis must at least include testing to determine suitability from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done at H B Fuller/Royal Adhesives & Sealants Canada Ltd. All technical assistance and information provided with respect to H B Fuller/Royal Adhesives & Sealants Canada Ltd.'s products are subject to H B Fuller/Royal Adhesives & Sealants Canada Ltd.'s Terms and Conditions, including the limited warranty therein. H B Fuller/Royal Adhesives & Sealants Canada Ltd.'s Terms and Conditions appear on H B Fuller/Royal Adhesives & Sealants Canada Ltd.'s credit applications and invoices and are available upon your request. Except as expressly provided in the Terms and Conditions, H B Fuller/Royal Adhesives & Sealants Canada Ltd. excludes all express and implied warranties, representations, conditions and objections, whether statutory or otherwise, concerning the quality of the products of H B Fuller/Royal Adhesives & Sealants Canada Ltd. or their fitness for any particular purpose. It is expressly understood and agreed that the customer assumes and hereby expressly releases H B Fuller/Royal Adhesives & Sealants Canada Ltd. from all liability, in tort, contract, or otherwise, incurred in connection with the use of our products, technical assistance and information. Any statement or recommendation not contained herein is unauthorized and shall not bind H B Fuller/Royal Adhesives & Sealants Canada Ltd. Nothing herein shall be construed as a recommendation to use any product in conflict with patents covering any material or its use. No license is implied or in fact granted under the claims of any patent.